



8 Software-Selectable Input Channels

Product Sheet

System 8000 Micro-Measurements

StrainSmart® Data Acquisition System

Features

- Eight software-selectable input channels
- Up to 16 scanners can be used concurrently
- Supported inputs include:
 - Strain gage (quarter-, half-, and full-bridges)
 - Strain-gage-based transducer
 - High-level voltage signal
 - Thermocouples
- RJ45 input connectors for each input channel
- Scanning rates:
 - 1000, 500, 200, 100, and 10 samples/second
- Compact size and ruggedized enclosure
- Ethernet network architecture
- Optional self-calibration functionality available

StrainSmart® Data Acquisition System



Revision 19-Oct-2012

system and excitation power requirements. The total system power requirements are highly dependent upon the power requirements of the bridge excitation circuitry. At a minimum, the instrument requires approximately 17 watts of power. A fully loaded instrument employing the maximum excitation current requires up to 26 watts of power.

ENCLOSURE

The Model 8000-8-SM enclosure is constructed of aluminum alloy. The enclosure is designed to provide superior strength, durability, and to minimize RF emissions and susceptibility.

8000-SM-VC SYSTEM VOLTAGE CALIBRATION CARD (OPTIONAL)



The 8000-SM-VC System Voltage Calibration Card is available as an accessory and provides the ability to perform a system-level calibration of the entire measurement circuit without the need to return the system to the manufacturer or metrology lab. The gain and offset of each channel can be calibrated. The 8000-SM-VC is calibrated at the factory to NIST-traceable standards and does not need to be present in the system during normal operation. A benefit of on-board system calibration is the ability to calibrate the system under the actual operating conditions, thereby minimizing errors due to environmental conditions.

SPECIFICATIONS – GENERAL

All specifications are nominal or typical at +23°C unless noted. Performance may be degraded in the presence of high-level electromagnetic fields. For CE compliance, Micro-Measurements recommends that all cables be limited to 30 meters in length.

Environmental

Temperature: 0° to +50°C

Humidity: Up to 90%, non-condensing

Enclosure

Material: A356-T6 aluminum casting

Dimensions (all dimensions are nominal):
1.72 H (1.96 with feet) x 11.0 W x 10.18 D
(10.55 including power connector) inches
(43.68 x 279.4 x 258.66 mm)

Configurations:
Bench-top, stackable, rack-mountable.

Weight

3.95 lbs (1.75 kg)

- Eight software-selectable input channels
- Up to 16 scanners can be used concurrently
- Supported inputs include:
 - Strain gage (quarter-, half-, and full-bridges)
 - Strain-gage-based transducer
 - High-level voltage signal
 - Thermocouples
- RJ45 input connectors for each input channel
- Scanning rates are 1000, 500, 200, 100, and 10 samples/second
- Compact size and ruggedized enclosure
- Ethernet network architecture
- Optional self-calibration functionality available

DESCRIPTION

System 8000 from Micro-Measurements is a versatile, precision data acquisition instrument system intended for static and dynamic test and measurement applications. The system includes a scanner with 8 channels of data acquisition. A 10' crossover Ethernet cable is also included. A 10' crossover Ethernet cable is also included. The scanners may be used separately or up to 16 scanners can be used concurrently for a maximum of 128 channels.

Each channel can be configured, via software, to accept signals from strain gages or strain-gage-based transducers, thermocouples, or high level voltage sensors. Strain gage channels accept full-, half-, or quarter-bridge configurations and have the required bridge completion components for 120-, 350-, and 1000-ohm bridges. Each scanner operates independently, multiple scanners are not synchronized.

The data is processed in a modern 24-bit digital signal processor and filtering is performed using Finite Impulse Response (FIR), multi-stage filters. This provides excellent noise rejection and stability and unsurpassed measurement accuracy.

The Model 8000-8-SM Scanner communicates with a host personal computer (PC) via an Ethernet connection. Micro-Measurements StrainSmart® software is optimal for configuring, controlling, and acquiring data from the System 8000. A Programmer's Reference Kit provides documentation, programming examples, and instrument drivers to assist with custom software development.

SUPPORTED SENSORS

Each channel can be defined, via software, to be one of the following sensor types:

- Strain gage (quarter-, half-, and full-bridges)
- Strain-gage-based transducer
- High-level voltage signal
- Thermocouples

SAMPLING

All channels in each scanner are sampled simultaneously. Each channel's 24-bit analog-to-digital converter oversamples data at a rate of 128k samples/second, and provides high quality, low noise data (without the need for signal averaging) at rates up to 1000 samples/second/channel.

SCANNING RATES

The system provides numerous scan rates and Finite Impulse Response (FIR) filters are automatically selected to provide suitable filtering at each rate to avoid aliasing. Sampling rates for the Model 8000-8-SM are 1000, 500, 200, 100, and 10 samples/second.

COMPACT, RUGGEDIZED ENCLOSURE

The Model 8000-8-SM has 8 channels in a 1U (1.72 inch) height enclosure. The aluminum-alloy enclosure provides superior strength and durability. A rack mount kit is also available.

RJ45 INPUT CONNECTORS

Each channel input connector is an 8-pin TIA/EIA RJ45.

RELAY OUTPUT

Relay output is provided to control external hardware.

ETHERNET NETWORK ARCHITECTURE

The system communicates over an IEEE-802.3u 100Base-TX or an IEEE-802.3 10Base-T Ethernet Network. The firmware uses separate command and data ports and employs a reliable TCP-based protocol to prevent data loss.

DC OPERATION

Model 8000 operates on 10-32 VDC power. This can be from the included power supply or by using a separate AC-to-DC converter or DC supply such as a battery.

MODEL 8000-8-SM POWER SOURCE

The Model 8000 is a DC-powered instrument. The system accommodates DC input voltages from 10 to 32 volts. The included power supply provides the required AC-to-DC conversion and up to 30 watts of power to the system. An alternate DC power source can be used provided that it supplies enough power to meet the

Power

Input: 10-32 VDC, 5A max.

Fuse: 5A Fast-acting blade terminal. (Littelfuse FUN MINI® PN 125-6785-4502 or equivalent)

Power Switch:

Rockler switch with green LED to indicate power on.

Relay

Quantity: One

Configuration: NO and NC, 500 mA relay contact

Communication

Ethernet interface: IEEE 802.3 10Base-T, 802.3u 100Base-TX, half- and full-duplex, auto-detect, RJ45 connection, green LINK/ACT LED

8000-SM-VC Voltage Calibration Card

Accuracy: ±100 ppm repeatability, typical

±250 ppm repeatability, maximum

Drift:

1.9 ppm/°C ±0.6 µV/°C typical

9.4 ppm/°C ±2.1 µV/°C maximum

Resolution: 150 µV nominal

Voltage Range: ±5V

ANALOG CHANNELS

Channels

Eight, differential inputs

A/D Converter

Quantity: Eight (one per channel)

Architecture: Delta-Sigma (ΔΣ)

Resolution: 24 bits

Oversampling Rate:

128k samples/second/channel (max)

Data Rates

1000, 500, 200, 100, or 10 samples/second/channel

Analog Anti-Alias Filter

Type: Low-pass

Frequency: 500 Hz @ -3 dB

Number of Poles: One

Topology: Lowpass RC

Processor

Type: 32-bit floating point Digital Signal Processor

300 MHz operating frequency

RAM


Type: SDRAM

Size: 32 MB

Flash

Type: Serial NOR

Size: 1MB (user)



DISCLAIMER: ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE. Vishay Precision Group, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf collectively, "Vishay Precision Group," disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product. The product specifications do not extend to, and are not intended to, be a warranty, representation or guarantee of any kind, in any form, in any medium, and under any conditions of purchase, including but not limited to, the warranty expressed therein. Vishay Precision Group disclaims all liability for any and all liability arising out of the application or use of any product, (b) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability. Information provided in databases and/or specifications may vary from actual results in different applications and performance may vary over time. Statements regarding the suitability of products for certain types of applications are based on Vishay Precision Group's knowledge of typical requirements that are often placed on Vishay Precision Group products. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. No license, express, implied, or otherwise, to any intellectual property rights is granted by this document, or by any conduct of Vishay Precision Group. The products shown herein are not designed for use in life-saving or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay Precision Group products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay Precision Group for any damages arising or resulting from such use or sale. Please contact authorized Vishay Precision Group personnel to obtain written terms and conditions regarding products designed for such applications. Product names and markings noted herein may be trademarks of their respective owners.